



高新技术企业/专精特新企业
专业的高温加热制造工厂 (-60°C~2600°C)

中国热处理行业协会理事单位
ISO45001:职业健康安全管理体系认证
ISO14001:环境管理体系认证
ISO9001:质量管理体系认证
欧盟CE产品认证



电话/邮箱
13271526781
+86 379-69936789
thermo@gwdl.com

GWDL-1100 °C Vacuum Distillation Furnace



Technical parameters:

category parameter	1100y
Voltage AC	380V/12KW
Maximum operating temperature	1100y
Long-term operating temperature	Long-term y1100y
Temperature control accuracy	±1 degree
Equipment dimensions	Approximate dimensions: 5500mm wide * 1000mm deep * 1500mm high
Heating rate,	Up to 15°C per minute (non-linear)
furnace tube material/size (mm)	Quartz tube diameter 150*1400mm, wall thickness 5mm, one-section flange seal with vacuum interface, with... The air intake valve has an oval end cap at the other end of the quartz tube. The quartz tube is horizontally mounted and can slide.
Temperature measurement	Two-zone heating, two zones with independent temperature control
in heating zone	K-type temperature measurement range: 0-1250y

Main website: www.gwdl.com Email: thermo@gwdl.com Contact: 13271526781 0379-69936789

Address: No. 1, Xingye 1st Road, Science and Technology Industrial Park, Jianxi District, Luoyang City, Henan Province

Main station: www.gwdl.com Email: thermo@gwdl.com Contact information:13271526781 0379-69936789

Add: No. 1, Xingye 1st Road, Science and Technology Industrial Park, Jianxi District, Luoyang City, Henan Province



高新技术企业/专精特新企业
专业的高温加热制造工厂 (-60°C~2600°C)

中国热处理行业协会理事单位
ISO45001:职业健康安全管理体系认证
ISO14001:环境管理体系认证
ISO9001:质量管理体系认证
欧盟CE产品认证



电话/邮箱
13271526781
+86 379-69936789
thermo@gwdl.com

Temperature control programming curve segment number	Xiamen Yudian High Precision 8 Series 50-Segment Program
The electric furnace is equipped with a 7-inch touchscreen for centralized control.	
The heating element has an inner diameter of 170mm in the heating zone and is made of high-temperature alloy resistance wire from Beijing Shougang (containing molybdenum surface temperature).	(1450 degrees), installation location around the furnace tubes
The vacuum pump system's molecular pump unit can connect to up to three devices. Vacuum level less than 6.0 x 10 ⁻⁴ Pa	
Refractory materials	1700 type high temperature alumina fiber
Furnace body temperature	γ45 degrees
Warranty coverage and period	The electric furnace comes with a one-year free warranty, but the heating element and furnace tube are not covered by the warranty.
Random spare parts	One instruction manual, one certificate of conformity, one crucible tong, and one pair of high-temperature gloves.

Thank you for contacting us!

Thank you to get in touch with us!

Company Name: Luoyang Juxing Kiln Co., Ltd.

Company Name: Luoyang Ju Xing Kiln Co., Ltd. Company Address: No. 1, Xingye 1st Road, Jianxi Science and Technology Industrial Park, Luoyang City

Company Address: No. 1, Xingye Road, Jianxi Science and Technology Industrial Park, Luoyang City

Contact information: 13271526781, 0379-69936789, thermo@gwdl.com

Website: www.gwdl.com www.gwdlcom.cn www.gwdl.org www.gwdl.cn